# PALOMAT<sup>®</sup> AMR



PALOMAT® AMR is CE approved and compliant with the latest Machinery Directive. This is your guarantee for a product in accordance with the given health, safety and environment requirements. When PALO-MAT<sup>®</sup> AMR is integrated into a solution, the responsibility of the overall CE approval shifts to the project manager/integrator in question.

## Includes:

- Safety frame for 15 EUR-pallets
- Maximum indicator for 15 EUR-pallets
- Technical documentation
- Example sequence diagram for programming

PALOMAT® AMR is delivered with a WISE 4060 module with I/O signals, making it possible to exchange signals between the PALOMAT® and MiR Mobile Robot.

## WISE module interface specifications:

#### Outputs: [puls 3-4 sec.]

- Signal 0 Choose destacking .
- Signal 1 – Choose stacking
- Signal 2 Emptying the PALOMAT<sup>®</sup> (full stack)
- Signal 3 Not used

#### Inputs: [continuous signal]

- Signal 0 PALOMAT<sup>®</sup> empty (destacking)
- Signal 1 New pallet ready to be picked up
- Signal 2 PALOMAT<sup>®</sup> full (stacking) .
- Signal 3 – PALOMAT<sup>®</sup> ready for pallet

## Standard colour:



## **Technical specifications:**

- Article no.: 152800
- Actuator: Linak
- Steering: Siemens S7-1200
- Power source: 220-240VAC 50Hz 1P+ N + PE
- Capacity: 15 EUR-pallets, 1200 x 800 x 144 mm/ 500 kg
- Cycle time per pallet: 10-15 sec.
- Compatiable with MiR500 and MiR1000 with an EU Pallet Lift from Mobile Industrial Robots A/S.

### Service:

- Technical hotline support: 24/7-365
- +45 96 69 47 10
- info@palomat.com



PALOMAT<sup>®</sup> • Industrivej 10 • DK-7900 Nykøbing Mors • Tlf.: +45 96 69 47 10 • Mail: info@palomat.com

